

Garant
HiPer-Drill cutter insert h7, HB7630, Ø D: 19,6 mm

Order data

Order number	231650 19,6
GTIN	4045197662248
Item class	21M

Description
Version:

Vee ground cutter inserts for precise positioning and stable seating.
Concentricity when assembled $\leq 20 \mu\text{m}$. For holes up to IT9 accuracy.

Note:

Further sizes available on request. Cutting data apply to 5×D drilling bodies.

Use exclusively cutter heads of the same type when drilling pilot holes.
for base body Ø D: 19 mm

Feed f in stainless steel $> 900 \text{ N/mm}^2$: 0.21 mm/rev.

Technical description

Feed f in stainless steel $> 900 \text{ N/mm}^2$	0.21 mm/rev.
Ø D	19.6 mm
for base body Ø D	19 mm
Number of changes/inserts	1
Grade	HB7630

Tool material	Carbide
Point angle	135 degrees
Number of cutting edges Z	2
Type of product	Cutter insert for boring

Accessories

Torx Plus® screw Drive 9IP	231999 9IP
----------------------------	------------