

Garant
HiPer-Drill cutter insert h7, HB7630, Ø D: 20,75 mm

Order data

Order number	231650 20,75
GTIN	4045197605047
Item class	21M

Description
Version:

Vee ground cutter inserts for precise positioning and stable seating.
Concentricity when assembled $\leq 20 \mu\text{m}$. For holes up to IT9 accuracy.

Note:

Further sizes available on request. Cutting data apply to 5×D drilling bodies.

Use exclusively cutter heads of the same type when drilling pilot holes.
for base body Ø D: 20 mm

Feed f in stainless steel $> 900 \text{ N/mm}^2$: 0.22 mm/rev.

Technical description

Ø D	20.75 mm
Feed f in stainless steel $> 900 \text{ N/mm}^2$	0.22 mm/rev.
for base body Ø D	20 mm
Number of changes/inserts	1
Grade	HB7630

Tool material	Carbide
Point angle	135 degrees
Number of cutting edges Z	2
Type of product	Cutter insert for boring

Accessories

Torx Plus® screw Drive 9IP	231999 9IP
----------------------------	------------