

Garant
QuickTurn clamping toolholder, right-hand, Shank / insert size: 20/08mm

Order data

Order number	251906 20/08
GTIN	4045197651211
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DWLNR/L 2025K08

suitable indexable insert: WN.. 0804..

Functional width L₄: 25 mm

Head length L₁: 32 mm

Overall length L: 125 mm

Shim: 259031 42

Technical description

suitable indexable insert	WN.. 0804..
Insert size	8 mm
Shank size	20 mm
Shim screw	259025 4
Clamp	259038 9
Functional width L ₄	25 mm
Shim	259031 42

Head length L ₁	32 mm
ISO code toolholder	DWLNR/L 2025K08
Overall length L	125 mm
Series	QuickTurn
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw	259353
Shim	259581
Shim screw Type 4	259025 4
Clamping claw Type 9	259038 9
Shim screw	259171
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 42	259031 42
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500