

**Garant**
**QuickTurn clamping toolholder, left-hand, Shank / insert size: 20/08mm**

**Order data**

Order number	251907 20/08
GTIN	4045197651235
Item class	21U

**Description**
**Advantage:**

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DWLNR/L 2025K08

suitable indexable insert: WN.. 0804..

Functional width L<sub>4</sub>: 25 mm

Head length L<sub>1</sub>: 32 mm

Overall length L: 125 mm

Shim: 259031 42

**Technical description**

ISO code toolholder	DWLNR/L 2025K08
Shim	259031 42
Head length L <sub>1</sub>	32 mm
Clamp	259038 10
Functional width L <sub>4</sub>	25 mm
suitable indexable insert	WN.. 0804..
Shank size	20 mm

Insert size	8 mm
Shim screw	259025 4
Overall length L	125 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle $\kappa$	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

## Accessories

Clamping claw Type 10	259038 10
Shim screw	259171
Shim	259581
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim Type 42	259031 42
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 4	259025 4
Clamping claw	259354