

Garant
Lever lock toolholder, left-hand, Shank / insert size: 25/08mm

Order data

Order number	251917 25/08
GTIN	4045197651402
Item class	21T

Technical description

Shim punches pack	259047 2
Lever screw	259018 2
Shim	259031 40
Shank size	25 mm
Lever	259015 2
ISO code toolholder	PWLNLR/L 2525M08
suitable indexable insert	WN.. 0804..
Functional width L ₄	32 mm
Shim pins pack	259044 2
Head length L ₁	21 mm
Insert size	8 mm
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins 10 pieces Type 2	259044 2
Shim Type 40	259031 40
Shim punches set 10 pieces Type 2	259047 2
Lever Type 2	259015 2
Lever screw Type 2	259018 2
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500