

**SNMG 120404, Grade: PR1325****Order data**

Order number	251162 PR1325
GTIN	4960664628193
Item class	25E

Description

SNMG 120404 PR1325 Grade: PR1325

Chip breaker: MQ

Cutting depth a_p : 0.4 - 1.5 mm

Feed f : 0.03 - 0.12 mm/rev.

Cutting speed v_c main application: 40 - 100 m/min

Technical description

Product name attribute	
Insert assignment	neutral
Indexable insert profile	
Type of product	