

SONO  SWISS®**Ultrasonic power cleaner, litres: T3****Order data**

Order number	082930 T3
GTIN	2050000969096
Item class	04E

Description**Version:**

High-yield water-based cleaning concentrate (exception: T3 supplied in powdered form); specially developed for use in ultrasonic cleaning baths; biologically degradable. The high-yielding **concentrates** extend the working life of the devices, last a long time, and are biologically degradable. The power cleaners have been specially developed for ultrasonic baths (foaming characteristics etc.) and are therefore particularly effective for all conventional ultrasonic cleaning baths operating at frequencies in the range 25 to 130 kHz. In conjunction with the cavitation forces created by the ultrasonic vibration the power cleaner releases the dirt gently but effectively whilst treating the components gently. Other cleaning agents which have not been developed specially for ultrasonic baths may under certain circumstances promote corrosion or removal of material. Halogen ions are an example of aggressive corrosion promoters which greatly reduce the working life. Chlorides and fluorides in acid media are the most aggressive in this respect.

Application:

For ultrasonic cleaning baths (such as No. 082922; 082923; 082924; 082925).

Note:

Other special cleaners and other container sizes available on request.

Unavailable in some countries.

See application table on the next catalogue page.

Labelling of hazardous substances: GHS05 corrosive

Labelling of hazardous substances: GHS07 caution
Manufacturer's designation: T3
Fill capacity powder: 0.85 kg

Technical description

Type of cleaning agent	Power cleaner for steel and light metals
Fill capacity powder	0.85 kg
Labelling of hazardous substances	GHS05 corrosive
Labelling of hazardous substances	GHS07 caution
Storage temperature	-5 - 30 °C
Mixing ratio	3 – 5 %
Processing time	3 - 10 min
UN number	UN3253
hazardous goods class	8
Manufacturer's designation	T3