

Garant
QuickTurn clamping toolholder DSSNR 45°, for indexable inserts SN., right-hand

Order data

Order number	251104 20/12
GTIN	4045197650757
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Technical description

Shim screw	259025 4
Functional width L ₄	32 mm
Shank size	20 mm
Shim	259031 21
Insert size	12 mm
Clamp	259038 8
suitable indexable insert	SN.. 1204..
Head length L ₁	49 mm
ISO code toolholder	DSSNR/L 2025K12
Overall length L	125 mm
Series	QuickTurn

Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 4	259025 4
Shim Type 21	259031 21
Clamping claw Type 8	259038 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15