


**SNMG 120408, Grade: CA6525**

**Order data**

Order number	251164 CA6525
GTIN	4960664513178
Item class	25E

**Description**

SNMG 120408 CA6525 Corner radius: 0.8 mm  
 Grade: CA6525  
 Chip breaker: MQ  
 Cutting depth  $a_p$ : 0.5 - 2 mm  
 Feed  $f$ : 0.05 - 0.25 mm/rev.  
 Cutting speed  $v_c$  main application: 60 - 220 m/min

**Technical description**

Chip breaker	MQ
Feed $f$	0.05 - 0.25 mm/rev.
Cutting depth $a_p$	0.5 - 2 mm
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Main application	M
Grade	CA6525

Cutting speed $v_c$ main application	60 - 220 m/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning