

Garant
QuickTurn clamp toolholder, left-hand, Shank / insert size: 20/12mm

Order data

Order number	251105 20/12
GTIN	4045197650771
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DSSNR/L 2025K12

suitable indexable insert: SN.. 1204..

Functional width L₄: 32 mm

Head length L₁: 49 mm

Overall length L: 125 mm

Shim: 259031 21

Technical description

Shim	259031 21
Shim screw	259025 4
Shank size	20 mm
Functional width L ₄	32 mm
suitable indexable insert	SN.. 1204..
ISO code toolholder	DSSNR/L 2025K12
Insert size	12 mm

Clamp	259038 8
Head length L ₁	49 mm
Overall length L	125 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	45 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim Type 21	259031 21
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw	259171
Clamping claw	259352
Shim screw Type 4	259025 4
Shim	259231
Clamping claw Type 8	259038 8