



Copy mill 0° negative, with threaded shank, Ø D / number of teeth Z: 25/3_ mm

Order data

Order number	212135 25/3_
GTIN	4045197192721
Item class	210

Description

Version:

Milling body with irregular pitch for smooth cutting.

- **High axial run-out accuracy and concentricity**
- **Stepless repositioning of the insert as the cutting edge wears.**

Description:

With threaded connection. RD.. 10 – ap max = 2.5 mm.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

$a_{p\max} = 2.5$ mm.

Milling head suitable for insert shape: round

Milling application: Circular milling

Milling application: Ramping

Spacing of the milling cutter's cutting edges: unequal spacing

Tool exchange: PowerCard

Technical description

Shank type	with threaded shank
Tool exchange	PowerCard
Milling application	Circular milling
Milling application	Ramping
Milling head suitable for insert shape	round
Machining strategy	
Direction of infeed	
Spacing of the cutters	unequal spacing

Setting angle κ

Type of product
