


KOMET KUB® V464 drill head, Ø DC: 110mm

Order data

Order number	236660 110
GTIN	4047109090552
Item class	24L

Description
Version:

Indexable drill holder (drill head) with indexable insert cartridges and BS® T connection, right-hand cutting. The indexable insert cartridge for the outer indexable insert is adjustable by +5mm on the Ø. Use with arbors in ABS® N and extensions ABS® T. Reliability up to 6×D.

Process reliability up to 6×D.
Application:

With centring point No. 236661 - 236662.
With indexable inserts No. 236740 - 237080.

Supplied with:

Drill head with cartridges.

Note:

Spare parts on request.

Technical description

Number of cutting edges Z	1
Centring tip size	80
Pack of insert screws	239655 15IP (6.3 Nm)
External Ø d ₁	107.5 mm

ISO code indexable insert	WOEX080404
ABS® T Ø d	63 mm
Nominal Ø D	110
Overhang L _A	85 mm
Shank	ABS
Use for drilling	Drilling blind holes
Use for drilling	limited cross-drilling
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Type of product	Indexable drill

Accessories

KOMET KUB® V464 centring point, HSS Type 80	236661 80
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torx Plus® insert screw set 10 pieces Drive 15IP	239655 15IP
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
KOMET KUB® V464 centring point, HSS Type 80	236662 80
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600