

**WNMG 080408, Grade: CA510****Order data**

Order number	252014 CA510
GTIN	4960664700370
Item class	25E

Description

WNMG 080408 CA510 Grade: CA510
Chip breaker: HQ
Cutting depth a_p : 0.5 - 2 mm
Feed f : 0.07 - 0.3 mm/rev.
Cutting speed v_c main application: 80 - 450 m/min

Technical description

Corner radius	0.8 mm
Cutting depth a_p	0.5 - 2 mm
Cutting conditions	continuous
Feed f	0.07 - 0.3 mm/rev.
Chip breaker	HQ
Main application	P
Cutting speed v_c main application	80 - 450 m/min
Grade	CA510

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6
Type of product	Indexable insert for turning