



Boring bar steel, right-hand, Shank Ø / insert size: 16/11mm



Order data

Order number	260338 16/11
GTIN	
Item class	25U

Description

Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

Technical description

ISO code toolholder	A16Q SDUCR/L11
Minimum pre-drill Ø D_{min}	23 mm
Overhang L_1	80 mm
Centre offset L_3	14.5 mm
Insert screw	269022 3
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Shank Ø D_s	16 mm
Application type	right-hand
Boring depth up to	5xD
Standard	DIN 8024
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 3	269022 3