



Steel boring bar A.. SDUCL 93°, for indexable inserts DC.., left-hand



Order data

Order number	260339 16/11
GTIN	4960664579600
Item class	25U

Description

Version:

Streamlined flutes for improved chip evacuation, reduced tendency to vibrate, stable machining conditions.

Technical description

Overhang L_1	80 mm
Centre offset L_3	14.5 mm
Minimum pre-drill $\varnothing D_{\min}$	23 mm
suitable indexable insert	DC.. 11T3..
ISO code toolholder	A16Q SDUCR/L11
Insert size	11 mm
Insert screw	269022 3
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Application type	left-hand
Boring depth up to	5×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/260339-16/11>