


**HOLEX**
**HOLEX Pro INOX solid carbide high-performance drill, plain shank DIN 6535  
HB, AlTiN, Ø DC m7: 6,5mm**

**Order data**

Order number	GG1286 6,5
GTIN	4067263106432
Item class	GGN

**Description**
**Version:**

Efficient drilling especially for use in **stainless and acid-resistant steels**.  
Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Shank Ø $D_s$	8 mm
Standard	DIN 6537
Nominal Ø $D_c$	6.5 mm
Tolerance nominal Ø	m7
Flute length $L_c$	53 mm
Contents	5

Overall length L	91 mm
Number of cutting edges Z	2
Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.09 mm/rev.
recommended maximum drilling depth L <sub>2</sub>	43.3 mm
Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Twist Drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	55 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	45 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	35 m/min	S
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

---

## Accessories

HOLEX Pro Inox solid carbide high-performance drill, plain shank  
DIN 6535 HA Ø DC m7 6,5 mm

---

122685 6,5