



## WNMG 080408, Grade: NL300

### Order data

Order number	252090 NL300
GTIN	5678037
Item class	28A

### Description

WNMG 080408 NL300 Grade: NL300

Chip breaker: 2N

Cutting depth  $a_p$ : 1 - 3.5 mm

Feed  $f$ : 0.15 - 0.45 mm/rev.

Cutting speed  $v_c$  main application: 60 - 380 m/min

Cutting speed  $v_c$  secondary application: 110 - 340 m/min

### Technical description

Indexable insert clearance angle	degrees
Product name attribute	
suitable for tool $\varnothing D$	mm
Insert assignment	neutral
Rake	degrees
Indexable insert profile	
Type of product	