



## Line Light work lamp, Type: 1600

### Order data

Order number	081340 1600
GTIN	5708997000588
Item class	08C

### Description

#### Version:

The Line Light work lamp is formed of an extruded acrylic profile with an **integral lens** (beam dispersion angle 75°). It is thus exceptionally **sturdy and shock-resistant**. It is thus designed for use under the **harsh conditions** and reliably provides strong and concentrated light in any working area. With **battery for mobile use** with additional torch on the end (150 lumen).

With 24 V DC input for direct connection to the machine or via transformer No. 081342 to the 230 V mains power supply.

The lamp can be rotated in its housing to give lighting without dazzle.

#### Function:

IP20: No protection against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and no protection against water.

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Application:

For installation at the **workplace or in the vehicle**.

#### Supplied with:

Work light, 2 clips and fittings, end piece, cable entry / clamp, 2 connection sleeves.

### Technical description

Number of LEDs	216
Power supply	Mains-powered
Illumination	1300 lm
IP Index of Protection	IP 67
Lamp replaceable	no
Light output	18 W

Nominal voltage	230 V
Spread angle	75 degrees
ATEX zone	no
Overall length	1600 mm
Head Ø	25 mm
Type of product	Desk lamp / workstation lamp

---

## Accessories

Sucker pad holder	081345
Magnetic holder	081344