



WNMG 080408, Grade: NL920

Order data

Order number	252090 NL920
GTIN	2050001938831
Item class	28A

Description

WNMG 080408 NL920 Grade: NL920
 Chip breaker: 2N
 Cutting depth a_p : 1 - 3.5 mm
 Feed f : 0.15 - 0.45 mm/rev.
 Cutting speed v_c main application: 40 - 230 m/min
 Cutting speed v_c secondary application: 80 - 160 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
suitable for tool $\varnothing D$	mm
Insert assignment	neutral
Rake	degrees
Indexable insert profile	
Type of product	