


WN.G 080404, Grade: CA4515


Order data

Order number	252112 CA4515
GTIN	4960664600410
Item class	25E

Technical description

Chip breaker	STD
Corner radius	0.4 mm
Cutting speed v_c main application	110 - 360 m/min
Feed f	0.05 - 0.7 mm/rev.
Cutting conditions	slightly interrupted
Cutting depth a_p	0.5 - 4.2 mm
Main application	K
Grade	CA4515
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 080404
Number of changes/inserts	6

Type of product

Indexable insert for turning