


DNMG 150608, Grade: CA4515

Order data

Order number	250797 CA4515
GTIN	
Item class	25E

Technical description

Cutting speed v_c main application	110 - 360 m/min
Cutting depth a_p	0.5 - 5 mm
Chip breaker	STD
Main application	K
Cutting conditions	slightly interrupted
Feed f	0.05 - 0.7 mm/rev.
Corner radius	0.8 mm
Grade	CA4515
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4

Type of product

Indexable insert for turning