



DNMG 150604, Grade: KW10

Order data

Order number	250796 KW10
GTIN	4960664224371
Item class	25E

Description

DNMG 150604 KW10 Grade: KW10

Chip breaker: AH

Cutting depth a_p : 0.8 - 3.5 mm

Feed f : 0.1 - 0.35 mm/rev.

Cutting speed v_c main application: 60 - 400 m/min

Technical description

Feed f	0.1 - 0.35 mm/rev.
Cutting speed v_c main application	60 - 400 m/min
Chip breaker	AH
Corner radius	0.4 mm
Main application	N
Cutting conditions	slightly interrupted
Cutting depth a_p	0.8 - 3.5 mm

Grade	KW10
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DNMG 150604
Number of changes/inserts	4
Type of product	Indexable insert for turning