

**DNMG 150604, Grade: PR1325****Order data**

Order number	250796 PR1325
GTIN	4960664628155
Item class	25E

Description

DNMG 150604 PR1325 Grade: PR1325
Chip breaker: MU
Cutting depth a_p : 0.5 - 3.5 mm
Feed f : 0.05 - 0.15 mm/rev.
Cutting speed v_c main application: 40 - 100 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Shim	
Indexable insert profile	neutral
Type of product	