


TNMG 160408, Grade: CA510

Order data

Order number	251474 CA510
GTIN	4960664699179
Item class	25E

Description

TNMG 160408 CA510 Grade: CA510

Chip breaker: PQ

Cutting depth a_p : 0.2 - 2.5 mm

Feed f : 0.13 - 0.4 mm/rev.

Cutting speed v_c main application: 180 - 590 m/min

Technical description

Feed f	0.13 - 0.4 mm/rev.
Corner radius	0.8 mm
Chip breaker	PQ
Cutting conditions	continuous
Main application	P
Cutting depth a_p	0.2 - 2.5 mm
Cutting speed v_c main application	180 - 590 m/min
Grade	CA510

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6
Type of product	Indexable insert for turning