

Garant**Eco-QuickTurn clamping toolholder DWLNL 95°, for indexable inserts WN., left-hand****Order data**

Order number	251903 25/08
GTIN	4045197651082
Item class	21U

Description**Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Technical description

Insert size	8 mm
Head length L ₁	32 mm
Shim	259031 19
Functional width L ₄	32 mm
suitable indexable insert	WN.. 0804..
Shim screw	259025 1
Clamp	259038 10

Data sheet

ISO code toolholder	DWLNRL 2525X08
Shank size	25 mm
Overall length L	103.5 mm
Series	Eco
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/251903-25/08>