

**TNMG 160408, Grade: HB7140****Order data**

Order number	251544 HB7140
GTIN	4045197664792
Item class	21G

Description

TNMG 160408 HB7140 Grade: HB7140
Chip breaker: V4M
Tolerance: M
Cutting depth a_p : 1 - 5 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 85 - 210 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Indexable insert profile	neutral
Type of product	