


VNMG 160404, Grade: CA4515

Order data

Order number	251822 CA4515
GTIN	4960664600373
Item class	25E

Technical description

Main application	K
Chip breaker	STD
Feed f	0.05 - 0.7 mm/rev.
Corner radius	0.4 mm
Cutting speed v_c main application	110 - 360 m/min
Cutting conditions	slightly interrupted
Cutting depth a_p	0.75 - 3 mm
Grade	CA4515
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VNMG 160404
Number of changes/inserts	4

Type of product

Indexable insert for turning