



DCGX 11T3005, Grade: SP4019



Order data

Order number	260371 SP4019
GTIN	2050001939173
Item class	28D

Description

DCGX 11T3005 SP4019 Grade: SP4019

Chip breaker: 62

Cutting depth a_p : 0.15 - 3 mm

Feed f : 0.05 - 0.3 mm/rev.

Cutting speed v_c main application: 30 - 440 m/min

Technical description

Chip breaker	62
Cutting speed v_c main application	30 - 440 m/min
Feed f	0.05 - 0.3 mm/rev.
Cutting depth a_p	0.15 - 3 mm
Cutting conditions	continuous
Main application	UNI
Grade	SP4019
Finishing/roughing assignment	Finishing

Tool material	HM
Series	eco screw-on toolholder
Series	Screw-on toolholder
Series	Boring bar
Series	Cutting head
ISO code indexable insert	DCGX 11T3005
Number of changes/inserts	2
Insert assignment	neutral