

**Garant****Arbor for screw-in milling cutter, cylindrical, PSC 63, Thread size M: M12X50****Order data**

|              |               |
|--------------|---------------|
| Order number | 308553 M12X50 |
| GTIN         | 4067263110101 |
| Item class   | 31A           |

**Description****Version:**

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

**Application:**

To take screw-in milling cutters with thread.

**Technical description**

|                          |                      |
|--------------------------|----------------------|
| Bore $\varnothing D_1$   | 12.5 mm              |
| Reach $L_1$              | 50 mm                |
| Overhang dimension A     | 74.5 mm              |
| Thread M                 | M12x50               |
| External $\varnothing D$ | 21 mm                |
| Adapter                  | PSC 63               |
| Arbor standard           | ISO 26623-1          |
| Through-coolant          | yes                  |
| Concentricity            | $\leq 3 \mu\text{m}$ |

|                    |                          |
|--------------------|--------------------------|
| Machining strategy | HPC                      |
| Type of product    | Threaded copy mill arbor |