

Garant

eco lever lock toolholder, short, right-hand, Shank / insert size: 16/08 mm



Order data

Order number	251904 16/08
GTIN	4045197651129
Item class	21U

Description

Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Through-coolant: yes

ISO code toolholder: PWLNR/L 1620X08

suitable indexable insert: WN.. 0804..

Functional width L₄: 25 mm

Head length L₁: 34 mm

Overall length L: 81 mm

Shim: 259031 19

Technical description

Lever	259015 3
Insert size	8 mm
ISO code toolholder	PWLNR/L 1620X08
Shank size	16 mm
Lever screw	259018 3

Functional width L ₄	25 mm
Shim	259031 19
Spring	259046 1
suitable indexable insert	WN.. 0804..
Head length L ₁	34 mm
Overall length L	81 mm
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	95 °
Type of product	Boring bar

Accessories

PrecisionBit for hex, shank E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Lever screw Type 3	259018 3
Spring Type 1	259046 1
Shim Type 19	259031 19
Lever Type 3	259015 3