

Garant
ER collet chuck, PSC 32 short, for ER collet size: 20

Order data

Order number	308512 20
GTIN	4067263110132
Item class	31A

Description
Version:

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For clamping tools with plain shank in ER collets to DIN 6499 Form A and B.

Supplied with:

Coated High-Speed clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck key No. 309680 or 613300.

Technical description

Overhang dimension A	50 mm
Clamping range	1 - 13 mm
for ER collets	20
Spare GARANT high-speed clamping nut No. 309610	20
External Ø D	34 mm
Adapter	PSC 32 short
Arbor standard	ISO 26623-1

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Through-coolant	yes
Type of product	Collet chuck