



DNMG 150612, Grade: CA525

Order data

Order number	250798 CA525
GTIN	4960664680849
Item class	25E

Description

DNMG 150612 CA525 Grade: CA525

Chip breaker: PS

Cutting depth a_p : 1 - 4 mm

Feed f : 0.15 - 0.6 mm/rev.

Cutting speed v_c main application: 70 - 420 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Shim	
Indexable insert profile	neutral
Type of product	