



Soldering station, Manufacturer's designation: PICOMK2



Order data

Order number	082301 PICOMK2
GTIN	4003008089288
Item class	04K

Description

Version:

Temperature-controlled soldering station with ceramic PTC heating element and internally-heated Ersadur long-life soldering tips (precise temperature control). Simple i-CON PICO operating concept, for entry-level users. Universal application. Very small footprint and smart functions, can be set using a micro-SD card.

Application:

For all professional electronics and electrical soldering applications.

Technical description

Warm-up time to 280 °C	9 s
AC supply voltage	240 V
electrostatic characteristic	EGB/ESD
Power supply	Mains-powered
Length	145 mm
Mains frequency	50 Hz
Weight of soldering iron without power cable	30 g
Control range of soldering tip temperature	150 - 450 °C
Height	103 mm

Width	80 mm
Power consumption	80 W
Type of product	Soldering station