

Garant
eco QT clamping toolholder, left-hand, Shank / insert size: 20/08mm

Order data

Order number	251903 20/08
GTIN	4045197651075
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Through-coolant: yes

ISO code toolholder: DWLNR/L 2025X08

suitable indexable insert: WN.. 0804..

Functional width L₄: 32 mm

Head length L₁: 32 mm

Overall length L: 91 mm

Shim: 259031 19

Technical description

ISO code toolholder	DWLNR/L 2025X08
Insert size	8 mm
Shim	259031 19

suitable indexable insert	WN.. 0804..
Shim screw	259025 1
Clamp	259038 10
Shank size	20 mm
Functional width L ₄	32 mm
Head length L ₁	32 mm
Overall length L	91 mm
Series	Eco
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping claw	259354
Shim	259214
Clamping claw Type 10	259038 10
Shim screw Type 1	259025 1
Shim Type 11	259031 11
Shim	259218
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim Type 19	259031 19
Shim screw	259167

