



DNMG 150608, Grade: CA525

Order data

Order number	250892 CA525
GTIN	4960664680900
Item class	25E

Description

DNMG 150608 CA525 Grade: CA525

Chip breaker: PH

Cutting depth a_p : 1 - 5 mm

Feed f : 0.25 - 0.8 mm/rev.

Cutting speed v_c main application: 70 - 420 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Shim	
Indexable insert profile	neutral
Type of product	