



ONE-KEY™ cordless hammer drill / driver, Type: M18OPD3-5



Order data

Order number	070102 M18OPD3-5
GTIN	4058546476724
Item class	03L

Description

Version:

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ ONE-KEY™ – latest generation of the FUEL™ devices with **integral Bluetooth technology for individual configuration, online stock management and device reporting.**

Supplied with:

Supplied with 2× Li-ion batteries, charger, carrying case (HD box) and belt clip.

Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.
The suitable Bluetooth tracking module can be found under 070103 BTT-1.

Technical description

Quick-clamping chuck range	1.5 - 13 mm
Battery capacity	5 Ah
Power supply	Mains operated
Manufacturer's designation	M18ONEPD3-502X
Weight	2.2 kg
maximum speed 1st speed	0 - 500 min ⁻¹
maximum torque	158 Nm
typical application	Heavy Duty
maximum vibration to EN with hammer drill function	11.3 m/s ²
Number of rechargeable batteries contained	2
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN without hammer drill function	1.5 m/s ²
Motor design	FUEL™
maximum twist drill size Ø in concrete	16 mm
maximum twist drill size Ø in wood	89 mm
App link	OneKey
maximum speed 2nd speed	2100 min ⁻¹
maximum twist drill size Ø in steel	16 mm
Type of rechargeable battery	Lithium-ion
Type of product	limpact drill /screwdriver