


**CCMT 060204, Grade: NL300**
**Order data**

Order number	260181 NL300
GTIN	5678030
Item class	28A

**Description**

CCMT 060204 NL300 Grade: NL300

Chip breaker: 73

Cutting depth  $a_p$ : 0.2 - 5 mm

Feed  $f$ : 0.1 - 0.45 mm/rev.

Cutting speed  $v_c$  main application: 60 - 380 m/min

Cutting speed  $v_c$  secondary application: 110 - 340 m/min

**Technical description**

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	neutral
Rake	degrees
Shim	
Indexable insert profile	
Type of product	