


TNMG 160404, Grade: CA510

Order data

Order number	251472 CA510
GTIN	4960664699162
Item class	25E

Technical description

Cutting speed v_c main application	180 - 590 m/min
Cutting depth a_p	0.2 - 2.5 mm
Corner radius	0.4 mm
Main application	P
Cutting conditions	continuous
Chip breaker	PQ
Feed f	0.13 - 0.4 mm/rev.
Grade	CA510
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Type of product

Indexable insert for turning