

Garant**Eco clamping toolholder PWLNL 95°, for indexable inserts WN., left-hand****Order data**

Order number	251905 25/06
GTIN	4045197651174
Item class	21U

Description**Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Technical description

Functional width L ₄	32 mm
Insert size	6 mm
Head length L ₁	30 mm
suitable indexable insert	WN.. 0604..
Shank size	25 mm
Spring	259046 2
Lever	259015 6
Shim	259031 9
ISO code toolholder	PWLNLR/L 2525X06

Data sheet

Lever screw	259018 4
Overall length L	101.5 mm
Series	Eco
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/251905-25/06>