

Garant
QuickTurn clamping toolholder DWLNR 95°, for indexable inserts WN., right-hand

Order data

Order number	251906 25/08
GTIN	4045197651228
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Technical description

suitable indexable insert	WN.. 0804..
Shank size	25 mm
Head length L ₁	32 mm
Shim screw	259025 4
Shim	259031 42
ISO code toolholder	DWLNR/L 2525M08
Clamp	259038 9
Insert size	8 mm
Functional width L ₄	32 mm
Overall length L	150 mm
Series	QuickTurn

Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 4	259025 4
Shim Type 42	259031 42
Clamping claw Type 9	259038 9
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15