

Garant
Lever lock toolholder, left-hand, Shank / insert size: 16/08mm

Order data

Order number	251917 16/08
GTIN	4045197651389
Item class	21T

Technical description

ISO code toolholder	PWLNLR/L 1616H08
Shim pins pack	259044 2
Lever	259015 2
Head length L ₁	20 mm
suitable indexable insert	WN.. 0804..
Shim punches pack	259047 2
Functional width L ₄	25 mm
Lever screw	259018 2
Shank size	16 mm
Shim	259031 40
Insert size	8 mm
Overall length L	100 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Shim punches set 10 pieces Type 2	259047 2
Shim Type 40	259031 40
Lever screw Type 2	259018 2
Lever Type 9	259015 9
Set of shim pins 10 pieces Type 2	259044 2
Lever screw Type 8	259018 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500