

**SNMG 120404, Grade: CA525****Order data**

Order number	251162 CA525
GTIN	4960664681327
Item class	25E

Description

SNMG 120404 CA525 Grade: CA525

Chip breaker: PQ

Cutting depth a_p : 0.2 - 2.5 mm

Feed f : 0.13 - 0.4 mm/rev.

Cutting speed v_c main application: 105 - 435 m/min

Technical description

Product name attribute	
Insert assignment	neutral
Indexable insert profile	
Type of product	