

Garant
QuickTurn clamp toolholder, left-hand, Shank / insert size: 25/12mm

Order data

Order number	251105 25/12
GTIN	4045197650788
Item class	21U

Description
Advantage:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce non-productive times.

Consistent clamping force, high interchange accuracy, maintenance-free.

Through-coolant: no

ISO code toolholder: DSSNR/L 2525M12

suitable indexable insert: SN.. 1204..

Functional width L_4 : 32 mm

Head length L_1 : 49 mm

Overall length L: 150 mm

Shim: 259031 21

Technical description

Head length L_1	49 mm
Shank size	25 mm
suitable indexable insert	SN.. 1204..
ISO code toolholder	DSSNR/L 2525M12
Shim screw	259025 4
Clamp	259038 8
Insert size	12 mm

Shim	259031 21
Functional width L ₄	32 mm
Overall length L	150 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	45 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw Type 4	259025 4
Clamping claw Type 8	259038 8
Shim screw	259171
Shim	259231
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim Type 21	259031 21
Clamping claw	259352