



SNMG 120408, Grade: CA125P

Order data

Order number	251164 CA125P
GTIN	4960664015474
Item class	25E

Technical description

ISO code indexable insert	SNMG 120408
Chip breaker	PQ
Corner radius	0.8 mm
Main application	P
Number of changes/inserts	4
Cutting conditions	slightly interrupted
Cutting depth a_p	0.2 - 2.5 mm
Tool material	Carbide
Feed f	0.13 - 0.4 mm/rev.
Grade	CA125P
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	150 - 320 m/min

Type of product

Indexable insert for turning