



CNMG 190612, Grade: CA125P

Order data

Order number	250383 CA125P
GTIN	4960664013951
Item class	25E

Technical description

Chip breaker	PH
Tool material	Carbide
Main application	P
Cutting speed v_c main application	140 - 300 m/min
Feed f	0.28 - 0.88 mm/rev.
Corner radius	1.2 mm
ISO code indexable insert	CNMG 190612
Grade	CA125P
Finishing/roughing assignment	Roughing
Cutting depth a_p	1 - 10 mm
Number of changes/inserts	4
Cutting conditions	slightly interrupted

Type of product

Indexable insert for turning