



CNMG 160608, Grade: CA125P

Order data

Order number	250376 CA125P
GTIN	4960664013913
Item class	25E

Technical description

Number of changes/inserts	4
Cutting conditions	slightly interrupted
Tool material	Carbide
Feed f	0.28 - 0.88 mm/rev.
Main application	P
Corner radius	0.8 mm
ISO code indexable insert	CNMG 160608
Finishing/roughing assignment	Roughing
Chip breaker	PH
Cutting depth a_p	1 - 10 mm
Grade	CA125P
Cutting speed v_c main application	140 - 300 m/min

Type of product

Indexable insert for turning