

Garant
GARANT Master Tap machine tap HSS-E-PM 6GX, AlTiX, MF: 5X0,5

Order data

Order number	137161 5X0,5
GTIN	4067263106968
Item class	111

Description
Version:

GARANT Master Tap Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Tolerance class: ISO 3X/6GX. For components which are **galvanised** or shrink slightly when hardened.

Technical description

Shank square <input type="checkbox"/>	2.7 mm
Tool material	HSS E PM
Thread type	MF
Number of cutting edges Z	3
Thread depth	12.5 mm
Shank $\varnothing D_s$	3.5 mm
Thread \varnothing	5 mm
Number of clamping slots	3
Tapping hole \varnothing	4.5 mm
Standard	DIN 374
Tolerance class	ISO 3X 6GX

Overall length L	70 mm
Thread pitch	0.5 mm
Thread size	M5×0,5
Coating	AlTiX
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	121 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M

INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		