



CNMM 160608, Grade: CA125P

Order data

Order number	250496 CA125P
GTIN	4960664014019
Item class	25E

Technical description

Tool material	Carbide
Feed f	0.25 - 0.9 mm/rev.
Grade	CA125P
ISO code indexable insert	CNMM 160608
Cutting depth a_p	1 - 11 mm
Number of changes/inserts	4
Finishing/roughing assignment	Roughing
Cutting conditions	slightly interrupted
Chip breaker	PX
Corner radius	0.8 mm
Cutting speed v_c main application	140 - 300 m/min
Main application	P

Type of product

Indexable insert for turning