

**DNMG 150612, Grade: CA125P****Order data**

Order number	250798 CA125P
GTIN	4960664024346
Item class	25E

Technical description

Cutting depth a_p	0.5 - 5 mm
Tool material	Carbide
Main application	P
Feed f	0.15 - 0.6 mm/rev.
Cutting conditions	slightly interrupted
Chip breaker	PMG
Grade	CA125P
ISO code indexable insert	DNMG 150612
Corner radius	1.2 mm
Cutting speed v_c main application	150 - 320 m/min
Number of changes/inserts	4
Finishing/roughing assignment	Finishing

Type of product

Indexable insert for turning