


**DNMG 150612, Grade: CA125P**

**Order data**

Order number	250893 CA125P
GTIN	4960664015306
Item class	25E

**Technical description**

Tool material	Carbide
Number of changes/inserts	4
Corner radius	1.2 mm
Finishing/roughing assignment	Roughing
Feed f	0.25 - 0.6 mm/rev.
Main application	P
Chip breaker	PH
ISO code indexable insert	DNMG 150612
Cutting depth $a_p$	1 - 5 mm
Cutting conditions	slightly interrupted
Grade	CA125P
Cutting speed $v_c$ main application	140 - 300 m/min

Type of product

Indexable insert for turning